



# MASTER PL-T 4 Pin

## MASTER PL-T 32W/830/4P 1CT/5X10BOX

MASTER PL-T is an efficient compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic gear and is provided with a plug-in/pull-out lamp base.

### Product data

General Information	
Cap-Base	GX24Q-3 [ GX24q-3]
Life to 50% Failures Preheat (Nom)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	90 %
Light Technical	
Color Code	830 [ CCT of 3000K]
Luminous Flux (Nom)	2400 lm
Luminous Flux (Rated) (Nom)	2400 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (Rated) (Min)	75 lm/W
Color Rendering Index (Nom)	>80
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	88 %
LLMF 6000 h Rated	86 %
LLMF 8000 h Rated	84 %

LLMF 12000 h Rated	81 %
Operating and Electrical	
Power (Rated) (Nom)	32.0 W
Lamp Current (Nom)	0.320 A
Temperature	
Design Temperature (Nom)	28 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	4 Pins
Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	35 kWh

# MASTER PL-T 4 Pin


Product Data	
Full product code	871150061128470
Order product name	MASTER PL-T 32W/830/4P 1CT/5X10BOX
EAN/UPC - Product	8711500611284
Order code	927914783071
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	50
Material Nr. (12NC)	927914783071
Net Weight (Piece)	70.000 g
ILCOS Code	FSMH-32/30/1B-L/P-GX24q=3

## Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


## Dimensional drawing




PL-T 32W/830/4P M

Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 32W/830/4P 1CT/5X10BOX	41.0 mm	98.7 mm	123.0 mm	138.7 mm

## Photometric data





Lightcolor /830




Lightcolor /830

# MASTER PL-T 4 Pin

## Lifetime



### Life Expectancy 3 h cycle



### Life Expectancy 12 h cycle

### Lumen Maintenance 3 h and 12 h cycle

