

64617 S 75 W 12 V

Halogen lamps with reflector MR11



Product family features

- Xenon instead of krypton as the filler gas (XENOPHOT HLX versions)
- Luminous flux up to 10 % higher with same power consumption (XENOPHOT HLX versions)



Product datasheet

Technical data

Product information

Order reference	64617 S
-----------------	---------

Electrical data

Nominal voltage	12.0 V
Nominal wattage	75.00 W


Photometrical data

Maximum color temperature	3200 K
---------------------------	--------

Light technical data

Focal length	26.0 mm
--------------	---------

Dimensions & weight



Diameter	35.0 mm
Length	35.5 mm

Lifespan

Lifespan	25 h
----------	------

Additional product data

Coating	Dichroic
Base (standard designation)	G5.3
Product remark	Spot adjustment
Minimum diameter of lamp enclosure	35.0 mm

Capabilities

Product datasheet

Cooling	Forced
Burning position	p90/p15
Application	Other

Certificates & standards

EEL – Energy Label	B
--------------------	---

Country specific categorizations

Order reference	64617 S
-----------------	---------

Product datasheet



Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300461106	64617 S 75 W 12 V	Folding carton box 1	34 mm x 34 mm x 50 mm	0.06 dm ³	19.00 g
4050300664750	64617 S 75 W 12 V	Shipping carton box 20	191 mm x 134 mm x 83 mm	2.12 dm ³	448.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

References / Links

For further technical information please refer to the following OSRAM brochure:
“Technology and applications, Low-voltage tungsten-halogen lamps”
“Halogen lamps, low and medium voltage for entertainment, technical and medical applications” cross reference list

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.